


# Grypper G80

High performance, 0.8 mm+ pitch net zero package footprint engineering test sockets for BGA style packaged devices



Ironwood Electronics Grypper series test socket is the next best thing to not having a socket at all. With superior electrical performance, the Grypper series test sockets allow BGA packages to fit into the exact end-use location for sample boards, failure analysis and other applications, where the space is limited only to IC package itself. The BGA IC package simply snaps into the Grypper test sockets. The Grypper G80 test sockets with reduced force required for insertions are designed for high-ball count BGA IC packages with 0.8 mm pitch and 1.0 mm pitch. The G80 is ideal for various applications, such as failure analysis, system-level test, device development and characterization.

#### FEATURES AND BENEFITS

Package-size PCB footprint Since the PCB footprint of G80 is identical to the package, only one

PCB design is required, enabling a seamless transition from test and validation through production and reducing overall test costs

Low insertion force Unique contact design reduces the insertion force required to insert

and retain higher-ball-count packages safely and securely within the

test socket


No lid required The package snaps directly without a lid, enabling easy probing, scoping

and troubleshooting the backside of the device

Excellent signal performance A short signal path achieves low inductance and low insertion loss,


providing a nearly invisible electrical connection

#### **METHODOLOGY**



Cross section view of test socket and package.

www.ironwoodelectronics.com



Pitch (mm)	Ball Diameter* (mm)	Ball Exposure	
0.8	0.45±0.05	0.30 min	
0.8	0.50±0.05	0.325 min	
0.8	0.55±0.05	0.35 min	
1	0.60±0.05	0.375 min	
1	0.65±0.05	0.40 min	

<sup>\*</sup>Standard designs available. Contact Ironwood Electronics for designs for other dimensions.

## TEST SOCKET DESCRIPTION

The Grypper technology uses a high-frequency beam contact. The design allows the Grypper beam to snap onto the contact, while removing oxides, resulting in reliable test results. The G80, with its single beam and reduced insertion force, is ideal for high-ball count BGA IC packages.

#### **ELECTRICAL SPECIFICATIONS**

P2A** Configuration	0.8 mm Pitch, 0.5 mm Ball*	1.0 mm Pitch, 0.5 mm Ball
Loop inductance	0.90 nH	1.19 nH
Self inductance	0.61 nH	0.80 nH
Mutual inductance	0.080 nH	0.090 nH
Capacitance	0.224 pF	0.195 pF
Mutual capacitance	0.028 pF	0.023 pF
S21 Insertion loss	-1 dB @ 22 GHz	-1 dB @ 30.8 GHz
S11 Return loss	-20 dB @ 6.5 GHz	-20 dB @ 2.0 GHz
S41 Crosstalk (GSSG)	-20 dB @ 5.0 GHz	-20 dB @ 3.2 GHz
Impedance	63.4 Ω	78 Ω
Time delay	15.0 ps	16.0 ps
Current Carrying Capacity	2 A	2 A
CRES	$<$ 50 m $\Omega$	< 50 mΩ

<sup>\*</sup> Specification based on lab measurements. Contact factory for additional electrical reports on other pitches and ball sizes.

<sup>\*\*</sup>P2A refers to the standard GSG, one signal contact with two ground contacts, one on either side of the signal.

P8A* configuration	0.8 mm Pitch, 0.5 mm Ball	1.0 mm Pitch, 0.5 mm Ball
Loop inductance	0.75 nH	0.88 nH
Self inductance	0.61 nH	0.80 nH
Capacitance	0.300 pF	0.263 pF
S21 Insertion loss	-1 dB > 40 GHz	-1 dB > 40 GHz
S11 Return loss	-20 dB @ 18 GHz	-20 dB @ 6.0 GHz
Impedance	50 Ω	58 Ω
Time delay	13.9 ps	14.3 ps
Current Carrying Capacity	2 A	2 A
CRES	$<$ 50 m $\Omega$	$<$ 50 m $\Omega$
1001 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1		

<sup>\*</sup>P8A refers to one signal contact surrounded by eight ground contacts.


Contactor life	50 insertions
Insertion Force*	40 grams / contact
Contact Length	2.2 mm

<sup>\*</sup>Insertion force based on 0.8 mm pitch, 0.45 mm diameter SAC 305 solder balls.


## MATERIAL SPECIFICATIONS


Contact base material	Copper (Cu) alloy	
Contact plating	Gold (Au) over Nickel (Ni)	
Housing	Polyimide (Cirlex®)	
Environmental	-55° C to +155° C	

## PERFORMANCE



## **PERFORMANCE**






## OPTIONS/SPARES

Package press

The package press provides uniform surface to press the package into the socket

Extraction tool

This tool assists removing the device from the contactor







Extraction tool



## **B.C.E. s.r.l.**Via Regina Pacis, 54/c - 41049 SASSUOLO (MO) Italy Tel. +39 0536 811.616 r.a. - Fax +39 0536 811.500 www.bce.it - E-mail: bce@bce.it



